

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857933

Luminaire Tested: **LX4C40D010 EX4C409035 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409035 4LBMDH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2902.0 lumens
Efficiency: N/A
Efficacy: 61.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857933

CATALOG NUMBER: LX4C40D010 EX4C409035 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857933

CATALOG NUMBER: LX4C40D010 EX4C409035 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	429508
5°	423712
10°	403836
15°	373676
20°	336389
25°	279458
30°	203142
35°	131679
40°	79690
45°	41072
50°	18597
55°	11202
60°	7519
65°	5378
70°	4059
75°	2658
80°	1698
85°	1128



TEST NUMBER: P857933

CATALOG NUMBER: LX4C40D010 EX4C409035 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	321.6	11.1
10°-20°	819.9	28.3
20°-30°	927.1	31.9
30°-40°	560.3	19.3
40°-50°	196.2	6.8
50°-60°	50.2	1.7
60°-70°	19.2	0.7
70°-80°	6.4	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2068.6	71.3
0°-40°	2628.8	90.6
0°-60°	2875.3	99.1
0°-90°	2902.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2902.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3496	
5°	3436	322
15°	2938	820
25°	2062	927
35°	878	560
45°	236	196
55°	52	50
65°	18	19
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P857933

CATALOG NUMBER: LX4C40D010 EX4C409035 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3496.1
2.5°	3481.6
5°	3435.8
7.5°	3354.5
10°	3237.2
12.5°	3095.6
15°	2938.0
17.5°	2765.2
20°	2573.0
22.5°	2337.4
25°	2061.6
27.5°	1745.6
30°	1432.0
32.5°	1132.1
35°	878.0
37.5°	665.8
40°	496.9
42.5°	357.0
45°	236.4
47.5°	145.5
50°	97.3
52.5°	70.0
55°	52.3
57.5°	40.2
60°	30.6
62.5°	24.1
65°	18.5
67.5°	14.5
70°	11.3
72.5°	8.0
75°	5.6
77.5°	4.0
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)