

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858043

Luminaire Tested: **LX4C40D010 EX4C409840 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858043
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409840 4LBWLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3608.9 lumens
Efficiency: N/A
Efficacy: 76.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858043

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P858043

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P858043

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	216.2	6.0
10°-20°	682.4	18.9
20°-30°	1064.6	29.5
30°-40°	1035.8	28.7
40°-50°	517.4	14.3
50°-60°	80.1	2.2
60°-70°	9.7	0.3
70°-80°	2.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1963.2	54.4
0°-40°	2999.0	83.1
0°-60°	3596.5	99.7
0°-90°	3608.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3608.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2211	
5°	2240	216
15°	2410	682
25°	2339	1065
35°	1682	1036
45°	649	517
55°	66	80
65°	8	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P858043

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2211.2
2.5°	2219.5
5°	2240.1
7.5°	2273.2
10°	2314.6
12.5°	2368.2
15°	2409.6
17.5°	2442.7
20°	2446.9
22.5°	2417.9
25°	2339.4
27.5°	2223.6
30°	2078.9
32.5°	1897.2
35°	1682.2
37.5°	1446.5
40°	1198.6
42.5°	934.1
45°	648.9
47.5°	417.4
50°	252.1
52.5°	136.3
55°	66.3
57.5°	29.0
60°	16.6
62.5°	12.4
65°	8.3
67.5°	8.3
70°	4.1
72.5°	4.1
75°	4.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)