

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857954

Luminaire Tested: **LX4C40D010 EX4C409040 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P857954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409040 4LBMDH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2906.0 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857954

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P857954

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	430098
5°	424292
10°	404385
15°	374198
20°	336846
25°	279851
30°	203426
35°	131859
40°	79802
45°	41125
50°	18616
55°	11202
60°	7519
65°	5378
70°	4059
75°	2658
80°	1698
85°	1128



TEST NUMBER: P857954

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	322.1	11.1
10°-20°	821.0	28.3
20°-30°	928.4	31.9
30°-40°	561.0	19.3
40°-50°	196.5	6.8
50°-60°	50.3	1.7
60°-70°	19.3	0.7
70°-80°	6.5	0.2
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2071.4	71.3
0°-40°	2632.5	90.6
0°-60°	2879.3	99.1
0°-90°	2906.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2906.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3501	
5°	3440	322
15°	2942	821
25°	2064	928
35°	879	561
45°	237	197
55°	52	50
65°	18	19
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P857954

CATALOG NUMBER: LX4C40D010 EX4C409040 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3500.9
2.5°	3486.4
5°	3440.5
7.5°	3359.2
10°	3241.6
12.5°	3099.9
15°	2942.1
17.5°	2769.0
20°	2576.5
22.5°	2340.6
25°	2064.5
27.5°	1748.0
30°	1434.0
32.5°	1133.7
35°	879.2
37.5°	666.7
40°	497.6
42.5°	357.5
45°	236.7
47.5°	145.7
50°	97.4
52.5°	70.0
55°	52.3
57.5°	40.3
60°	30.6
62.5°	24.2
65°	18.5
67.5°	14.5
70°	11.3
72.5°	8.1
75°	5.6
77.5°	4.0
80°	2.4
82.5°	1.6
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)