

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P857980

Luminaire Tested: **LX4C40D010 EX4C409050 4LBNLI**

Issue Date: 1/21/2022



Test Information

Test Method: LM-79-08
Report Number: P857980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/21/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409050 4LBNLI
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 4LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3070.9 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P857980

CATALOG NUMBER: LX4C40D010 EX4C409050 4LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P857980

CATALOG NUMBER: LX4C40D010 EX4C409050 4LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90		
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73		
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66		
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63		
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	970911
5°	873717
10°	677323
15°	490243
20°	339448
25°	247467
30°	179806
35°	106393
40°	44744
45°	13951
50°	1816
55°	1007
60°	1155
65°	1366
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P857980

CATALOG NUMBER: LX4C40D010 EX4C409050 4LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	622.8	20.3
10°-20°	1066.2	34.7
20°-30°	847.4	27.6
30°-40°	448.6	14.6
40°-50°	77.3	2.5
50°-60°	5.8	0.2
60°-70°	2.9	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2536.4	82.6
0°-40°	2985.0	97.2
0°-60°	3068.1	99.9
0°-90°	3070.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3070.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7903	
5°	7085	623
15°	3854	1066
25°	1826	847
35°	709	449
45°	80	77
55°	5	6
65°	5	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P857980

CATALOG NUMBER: LX4C40D010 EX4C409050 4LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7903.0
2.5°	7699.5
5°	7084.8
7.5°	6280.8
10°	5429.5
12.5°	4606.6
15°	3854.5
17.5°	3154.5
20°	2596.4
22.5°	2170.8
25°	1825.6
27.5°	1546.6
30°	1267.5
32.5°	983.8
35°	709.4
37.5°	468.3
40°	279.0
42.5°	160.8
45°	80.3
47.5°	28.4
50°	9.5
52.5°	9.5
55°	4.7
57.5°	4.7
60°	4.7
62.5°	4.7
65°	4.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)