

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858075

Luminaire Tested: **LX4C40D010 EX4C409030 4LBWH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409030 4LBWH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3868.6 lumens
Efficiency: N/A
Efficacy: 59.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858075

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P858075

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	306335
5°	307505
10°	308441
15°	308455
20°	306777
25°	299587
30°	280015
35°	242482
40°	189401
45°	135900
50°	88300
55°	52840
60°	30935
65°	19855
70°	13219
75°	9968
80°	7429
85°	0



TEST NUMBER: P858075

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	237.5	6.1
10°-20°	684.2	17.7
20°-30°	1009.7	26.1
30°-40°	996.4	25.8
40°-50°	609.7	15.8
50°-60°	233.8	6.0
60°-70°	73.1	1.9
70°-80°	21.4	0.6
80°-90°	2.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1931.4	49.9
0°-40°	2927.7	75.7
0°-60°	3771.2	97.5
0°-90°	3868.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3868.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2494	
5°	2494	237
15°	2425	684
25°	2210	1010
35°	1617	996
45°	782	610
55°	247	234
65°	68	73
75°	21	21
85°	0	3
90°	0	



TEST NUMBER: P858075

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2493.5
2.5°	2498.8
5°	2493.5
7.5°	2488.3
10°	2472.5
12.5°	2451.5
15°	2425.2
17.5°	2393.7
20°	2346.5
22.5°	2294.1
25°	2210.1
27.5°	2105.0
30°	1973.9
32.5°	1811.1
35°	1616.8
37.5°	1401.5
40°	1181.0
42.5°	976.4
45°	782.2
47.5°	608.8
50°	462.0
52.5°	341.3
55°	246.7
57.5°	173.2
60°	125.9
62.5°	94.5
65°	68.3
67.5°	52.6
70°	36.8
72.5°	26.2
75°	21.0
77.5°	10.5
80°	10.5
82.5°	5.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)