

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858007

Luminaire Tested: **LX4C40D010 EX4C409830 4LBMDH**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858007
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-9)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409830 4LBMDH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2552.1 lumens
Efficiency: N/A
Efficacy: 54.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.83
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858007

CATALOG NUMBER: LX4C40D010 EX4C409830 4LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P858007

CATALOG NUMBER: LX4C40D010 EX4C409830 4LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	68	86	78	72	68	76	71	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	63	60	68	63	59		67	62	59		66
9	76	66	60	56	74	65	60	56	64	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	377725
5°	372632
10°	355147
15°	328626
20°	295834
25°	245773
30°	178657
35°	115812
40°	70083
45°	36121
50°	16360
55°	9831
60°	6585
65°	4709
70°	3556
75°	2373
80°	1486
85°	987



TEST NUMBER: P858007

CATALOG NUMBER: LX4C40D010 EX4C409830 4LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	282.9	11.1
10°-20°	721.0	28.3
20°-30°	815.3	31.9
30°-40°	492.7	19.3
40°-50°	172.6	6.8
50°-60°	44.1	1.7
60°-70°	16.9	0.7
70°-80°	5.7	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1819.2	71.3
0°-40°	2311.9	90.6
0°-60°	2528.7	99.1
0°-90°	2552.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2552.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3075	
5°	3022	283
15°	2584	721
25°	1813	815
35°	772	493
45°	208	173
55°	46	44
65°	16	17
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P858007

CATALOG NUMBER: LX4C40D010 EX4C409830 4LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3074.6
2.5°	3061.9
5°	3021.6
7.5°	2950.1
10°	2846.9
12.5°	2722.5
15°	2583.8
17.5°	2431.9
20°	2262.8
22.5°	2055.6
25°	1813.1
27.5°	1535.2
30°	1259.4
32.5°	995.6
35°	772.2
37.5°	585.5
40°	437.0
42.5°	314.0
45°	207.9
47.5°	128.0
50°	85.6
52.5°	61.5
55°	45.9
57.5°	35.3
60°	26.8
62.5°	21.2
65°	16.2
67.5°	12.8
70°	9.9
72.5°	7.0
75°	5.0
77.5°	3.6
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)