

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858481

Luminaire Tested: **LD4C20W2N2765D010 4LBMH_2700K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858481
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20W2N2765D010 4LBMH_2700K
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1343.0 lumens
Efficiency: N/A
Efficacy: 52.9 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 25.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858481

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858481

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	163604
5°	161220
10°	154489
15°	145909
20°	136203
25°	123639
30°	103231
35°	74778
40°	46813
45°	26756
50°	13952
55°	7818
60°	4988
65°	2936
70°	2191
75°	949
80°	1415
85°	0



TEST NUMBER: P858481

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	9.1
10°-20°	321.5	23.9
20°-30°	413.1	30.8
30°-40°	310.8	23.1
40°-50°	124.8	9.3
50°-60°	35.5	2.6
60°-70°	11.2	0.8
70°-80°	3.2	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	857.1	63.8
0°-40°	1167.9	87.0
0°-60°	1328.3	98.9
0°-90°	1343.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1343.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1332	
5°	1307	123
15°	1147	321
25°	912	413
35°	499	311
45°	154	125
55°	36	36
65°	10	11
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P858481

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1331.7
2.5°	1323.6
5°	1307.3
7.5°	1276.9
10°	1238.4
12.5°	1191.8
15°	1147.2
17.5°	1096.5
20°	1041.8
22.5°	983.1
25°	912.1
27.5°	826.9
30°	727.7
32.5°	616.2
35°	498.6
37.5°	389.1
40°	291.9
42.5°	214.8
45°	154.0
47.5°	105.4
50°	73.0
52.5°	50.7
55°	36.5
57.5°	26.4
60°	20.3
62.5°	14.2
65°	10.1
67.5°	8.1
70°	6.1
72.5°	4.1
75°	2.0
77.5°	2.0
80°	2.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)