

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858022

Luminaire Tested: **LX4C40D010 EX4C409835 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858022
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409835 4LBMH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2736.7 lumens
Efficiency: N/A
Efficacy: 58.2 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858022

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P858022

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	112	109	106	104		110	107	104	102		103	101	99		99	97	96		96	94	93
2	105	100	95	91		103	98	93	90		95	91	88		91	88	86		89	86	84
3	99	91	85	80		97	90	84	80		87	82	78		84	80	77		82	79	76
4	92	83	77	72		90	82	76	71		80	75	70		78	73	70		76	72	69
5	87	77	70	65		85	76	69	64		74	68	64		72	67	63		70	66	62
6	81	71	64	58		80	70	63	58		68	62	58		67	61	57		65	61	57
7	76	65	58	53		75	65	58	53		63	57	53		62	56	52		61	56	52
8	72	60	53	49		70	60	53	49		59	53	48		58	52	48		57	52	48
9	68	56	49	45		66	56	49	45		55	49	44		54	48	44		53	48	44
10	64	52	46	41		63	52	46	41		51	45	41		50	45	41		49	44	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	216714
5°	217541
10°	218210
15°	218215
20°	217012
25°	211925
30°	198078
35°	171528
40°	134008
45°	96131
50°	62460
55°	37376
60°	21892
65°	14041
70°	9339
75°	7073
80°	5235
85°	0



TEST NUMBER: P858022

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.0	6.1
10°-20°	484.0	17.7
20°-30°	714.3	26.1
30°-40°	704.9	25.8
40°-50°	431.3	15.8
50°-60°	165.4	6.0
60°-70°	51.7	1.9
70°-80°	15.1	0.6
80°-90°	2.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1366.3	49.9
0°-40°	2071.2	75.7
0°-60°	2667.9	97.5
0°-90°	2736.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2736.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1764	
5°	1764	168
15°	1716	484
25°	1563	714
35°	1144	705
45°	553	431
55°	174	165
65°	48	52
75°	15	15
85°	0	2
90°	0	



TEST NUMBER: P858022

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1764.0
2.5°	1767.7
5°	1764.0
7.5°	1760.3
10°	1749.2
12.5°	1734.3
15°	1715.7
17.5°	1693.4
20°	1659.9
22.5°	1622.9
25°	1563.4
27.5°	1489.1
30°	1396.3
32.5°	1281.3
35°	1143.7
37.5°	991.5
40°	835.6
42.5°	690.7
45°	553.3
47.5°	430.7
50°	326.8
52.5°	241.5
55°	174.5
57.5°	122.5
60°	89.1
62.5°	66.9
65°	48.3
67.5°	37.2
70°	26.0
72.5°	18.5
75°	14.9
77.5°	7.4
80°	7.4
82.5°	3.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)