

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858024

Luminaire Tested: **LX4C40D010 EX4C409835 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409835 4LBNH
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2273.9 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858024

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P858024

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	350747
5°	342948
10°	317086
15°	284518
20°	250455
25°	215558
30°	173579
35°	115557
40°	60108
45°	27208
50°	11812
55°	7925
60°	5086
65°	3605
70°	2981
75°	1946
80°	0
85°	0



TEST NUMBER: P858024

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.6	11.3
10°-20°	624.8	27.5
20°-30°	725.4	31.9
30°-40°	480.4	21.1
40°-50°	134.7	5.9
50°-60°	33.8	1.5
60°-70°	12.7	0.6
70°-80°	4.3	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1607.8	70.7
0°-40°	2088.3	91.8
0°-60°	2256.9	99.2
0°-90°	2273.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2273.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2855	
5°	2781	258
15°	2237	625
25°	1590	725
35°	770	480
45°	157	135
55°	37	34
65°	12	13
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P858024

CATALOG NUMBER: LX4C40D010 EX4C409835 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2855.0
2.5°	2842.6
5°	2780.9
7.5°	2673.6
10°	2541.8
12.5°	2393.4
15°	2237.0
17.5°	2084.5
20°	1915.7
22.5°	1759.1
25°	1590.2
27.5°	1429.6
30°	1223.6
32.5°	1005.2
35°	770.5
37.5°	552.1
40°	374.8
42.5°	243.0
45°	156.6
47.5°	94.8
50°	61.8
52.5°	45.2
55°	37.0
57.5°	28.9
60°	20.7
62.5°	16.5
65°	12.4
67.5°	8.3
70°	8.3
72.5°	4.1
75°	4.1
77.5°	4.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)