

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858489

Luminaire Tested: **LD4C20W2N2765D010 4LBMLI_3500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858489
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20W2N2765D010 4LBMLI_3500K
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, W2N2765 LEDS
AND 4LBMLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1920.0 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 25.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858489

CATALOG NUMBER: LD4C20W2N2765D010 4LBMLI_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P858489

CATALOG NUMBER: LD4C20W2N2765D010 4LBMLI_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	371853
5°	365529
10°	335861
15°	281262
20°	225340
25°	181059
30°	134780
35°	76998
40°	36132
45°	15341
50°	4893
55°	2485
60°	1720
65°	1337
70°	826
75°	0
80°	0
85°	0



TEST NUMBER: P858489

CATALOG NUMBER: LD4C20W2N2765D010 4LBMLI_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.0	14.3
10°-20°	612.7	31.9
20°-30°	609.1	31.7
30°-40°	331.7	17.3
40°-50°	76.7	4.0
50°-60°	10.8	0.6
60°-70°	4.0	0.2
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1495.9	77.9
0°-40°	1827.6	95.2
0°-60°	1915.1	99.7
0°-90°	1920.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1920.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3027	
5°	2964	274
15°	2211	613
25°	1336	609
35°	513	332
45°	88	77
55°	12	11
65°	5	4
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P858489

CATALOG NUMBER: LD4C20W2N2765D010 4LBMLI_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3026.8
2.5°	3019.8
5°	2964.0
7.5°	2850.2
10°	2692.3
12.5°	2460.0
15°	2211.4
17.5°	1965.2
20°	1723.6
22.5°	1526.2
25°	1335.7
27.5°	1154.5
30°	950.1
32.5°	722.5
35°	513.4
37.5°	346.1
40°	225.3
42.5°	141.7
45°	88.3
47.5°	51.1
50°	25.6
52.5°	13.9
55°	11.6
57.5°	7.0
60°	7.0
62.5°	4.6
65°	4.6
67.5°	2.3
70°	2.3
72.5°	2.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)