

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858034

Luminaire Tested: **LX4C40D010 EX4C409840 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409840 4LBMDLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3011.4 lumens
Efficiency: N/A
Efficacy: 64.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858034

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P858034

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		66
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	485910
5°	502479
10°	507577
15°	457226
20°	379977
25°	298096
30°	218165
35°	112737
40°	53549
45°	18834
50°	4262
55°	2763
60°	1941
65°	1453
70°	1042
75°	665
80°	495
85°	0



TEST NUMBER: P858034

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	389.2	12.9
10°-20°	990.2	32.9
20°-30°	1001.9	33.3
30°-40°	510.8	17.0
40°-50°	100.1	3.3
50°-60°	12.1	0.4
60°-70°	5.0	0.2
70°-80°	1.8	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2381.3	79.1
0°-40°	2892.1	96.0
0°-60°	3004.3	99.8
0°-90°	3011.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3011.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3955	
5°	4074	389
15°	3595	990
25°	2199	1002
35°	752	511
45°	108	100
55°	13	12
65°	5	5
75°	1	2
85°	0	0
90°	0	



TEST NUMBER: P858034

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMDLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3955.2
2.5°	3991.9
5°	4074.5
7.5°	4121.8
10°	4068.8
12.5°	3890.0
15°	3594.9
17.5°	3246.7
20°	2906.4
22.5°	2553.8
25°	2199.1
27.5°	1845.9
30°	1537.9
32.5°	1158.8
35°	751.7
37.5°	503.3
40°	333.9
42.5°	209.6
45°	108.4
47.5°	38.8
50°	22.3
52.5°	16.5
55°	12.9
57.5°	10.1
60°	7.9
62.5°	6.4
65°	5.0
67.5°	3.6
70°	2.9
72.5°	2.1
75°	1.4
77.5°	1.4
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)