

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858514

Luminaire Tested: **LD4C20W2N2765D010 4LBWH_4000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20W2N2765D010 4LBWH_4000K
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, W2N2765 LEDS
AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1659.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 25.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858514

CATALOG NUMBER: LD4C20W2N2765D010 4LBWH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P858514

CATALOG NUMBER: LD4C20W2N2765D010 4LBWH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	131367
5°	131869
10°	132271
15°	132275
20°	131549
25°	128464
30°	120069
35°	103979
40°	81229
45°	58273
50°	37862
55°	22661
60°	13268
65°	8517
70°	5675
75°	4272
80°	3184
85°	0



TEST NUMBER: P858514

CATALOG NUMBER: LD4C20W2N2765D010 4LBWH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.8	6.1
10°-20°	293.4	17.7
20°-30°	433.0	26.1
30°-40°	427.3	25.8
40°-50°	261.5	15.8
50°-60°	100.3	6.0
60°-70°	31.4	1.9
70°-80°	9.2	0.6
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	828.2	49.9
0°-40°	1255.5	75.7
0°-60°	1617.2	97.5
0°-90°	1659.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1659.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1069	
5°	1069	102
15°	1040	293
25°	948	433
35°	693	427
45°	335	261
55°	106	100
65°	29	31
75°	9	9
85°	0	1
90°	0	



TEST NUMBER: P858514

CATALOG NUMBER: LD4C20W2N2765D010 4LBWH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1069.3
2.5°	1071.6
5°	1069.3
7.5°	1067.1
10°	1060.3
12.5°	1051.3
15°	1040.0
17.5°	1026.5
20°	1006.2
22.5°	983.8
25°	947.7
27.5°	902.7
30°	846.4
32.5°	776.7
35°	693.3
37.5°	601.0
40°	506.5
42.5°	418.7
45°	335.4
47.5°	261.1
50°	198.1
52.5°	146.4
55°	105.8
57.5°	74.3
60°	54.0
62.5°	40.6
65°	29.3
67.5°	22.5
70°	15.8
72.5°	11.3
75°	9.0
77.5°	4.5
80°	4.5
82.5°	2.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)