

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858036

Luminaire Tested: **LX4C40D010 EX4C409840 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P858036
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409840 4LBMLI
Description:
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3419.9 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858036

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P858036

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1081197
5°	972967
10°	754256
15°	545926
20°	378016
25°	275581
30°	200234
35°	118481
40°	49844
45°	15532
50°	2007
55°	1135
60°	1302
65°	1541
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858036

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	693.5	20.3
10°-20°	1187.3	34.7
20°-30°	943.6	27.6
30°-40°	499.5	14.6
40°-50°	86.1	2.5
50°-60°	6.4	0.2
60°-70°	3.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2824.5	82.6
0°-40°	3324.1	97.2
0°-60°	3416.6	99.9
0°-90°	3419.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3419.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8801	
5°	7890	694
15°	4292	1187
25°	2033	944
35°	790	500
45°	89	86
55°	5	6
65°	5	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858036

CATALOG NUMBER: LX4C40D010 EX4C409840 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	8800.7
2.5°	8574.1
5°	7889.6
7.5°	6994.3
10°	6046.2
12.5°	5129.8
15°	4292.3
17.5°	3512.8
20°	2891.4
22.5°	2417.3
25°	2033.0
27.5°	1722.2
30°	1411.5
32.5°	1095.5
35°	790.0
37.5°	521.5
40°	310.8
42.5°	179.2
45°	89.4
47.5°	31.7
50°	10.5
52.5°	10.5
55°	5.3
57.5°	5.3
60°	5.3
62.5°	5.3
65°	5.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)