

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858537

Luminaire Tested: **LD4C25W2N2050D010 4LBNH_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2050D010 4LBNH_3000K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2050 LEDS
AND 4LBNH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1659.0 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858537

CATALOG NUMBER: LD4C25W2N2050D010 4LBNH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858537

CATALOG NUMBER: LD4C25W2N2050D010 4LBNH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	261272
5°	254797
10°	235114
15°	208155
20°	180732
25°	154586
30°	127446
35°	83927
40°	45113
45°	19980
50°	8104
55°	5847
60°	3710
65°	2645
70°	2191
75°	1424
80°	2122
85°	0



TEST NUMBER: P858537

CATALOG NUMBER: LD4C25W2N2050D010 4LBNH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	11.5
10°-20°	456.1	27.5
20°-30°	522.5	31.5
30°-40°	351.0	21.2
40°-50°	100.3	6.0
50°-60°	24.6	1.5
60°-70°	9.3	0.6
70°-80°	3.6	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1169.8	70.5
0°-40°	1520.8	91.7
0°-60°	1645.6	99.2
0°-90°	1659.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1659.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2127	
5°	2066	191
15°	1637	456
25°	1140	522
35°	560	351
45°	115	100
55°	27	25
65°	9	9
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P858537

CATALOG NUMBER: LD4C25W2N2050D010 4LBNH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2126.7
2.5°	2111.6
5°	2066.1
7.5°	1984.4
10°	1884.7
12.5°	1757.5
15°	1636.6
17.5°	1509.6
20°	1382.4
22.5°	1261.5
25°	1140.4
27.5°	1028.5
30°	898.4
32.5°	726.0
35°	559.6
37.5°	408.4
40°	281.3
42.5°	184.5
45°	115.0
47.5°	69.5
50°	42.4
52.5°	33.3
55°	27.3
57.5°	21.2
60°	15.1
62.5°	12.1
65°	9.1
67.5°	6.1
70°	6.1
72.5°	3.0
75°	3.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)