

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858079

Luminaire Tested: **LD4C40D010 EU4409030 4LBNH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858079
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C40D010 EU4409030 4LBNH
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBN TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2942.0 lumens
Efficiency: N/A
Efficacy: 45.3 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858079

CATALOG NUMBER: LD4C40D010 EU4409030 4LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P858079

CATALOG NUMBER: LD4C40D010 EU4409030 4LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	74	65	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	56	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	453808
5°	443703
10°	410249
15°	368105
20°	324034
25°	278875
30°	224577
35°	149496
40°	77765
45°	35200
50°	15271
55°	10238
60°	6560
65°	4680
70°	3843
75°	2563
80°	0
85°	0



TEST NUMBER: P858079

CATALOG NUMBER: LD4C40D010 EU4409030 4LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	333.3	11.3
10°-20°	808.4	27.5
20°-30°	938.6	31.9
30°-40°	621.6	21.1
40°-50°	174.3	5.9
50°-60°	43.8	1.5
60°-70°	16.5	0.6
70°-80°	5.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2080.2	70.7
0°-40°	2701.8	91.8
0°-60°	2919.9	99.2
0°-90°	2942.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2942.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3694	
5°	3598	333
15°	2894	808
25°	2057	939
35°	997	622
45°	203	174
55°	48	44
65°	16	16
75°	5	6
85°	0	0
90°	0	



TEST NUMBER: P858079

CATALOG NUMBER: LD4C40D010 EU4409030 4LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3693.9
2.5°	3677.8
5°	3597.9
7.5°	3459.2
10°	3288.6
12.5°	3096.7
15°	2894.2
17.5°	2696.9
20°	2478.5
22.5°	2275.9
25°	2057.3
27.5°	1849.6
30°	1583.1
32.5°	1300.6
35°	996.8
37.5°	714.3
40°	484.9
42.5°	314.3
45°	202.6
47.5°	122.7
50°	79.9
52.5°	58.6
55°	47.8
57.5°	37.4
60°	26.7
62.5°	21.4
65°	16.1
67.5°	10.7
70°	10.7
72.5°	5.4
75°	5.4
77.5°	5.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)