

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858553

Luminaire Tested: **LD4C25W2N2050D010 4LBWH_2000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2050D010 4LBWH_2000K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2000K, W2N2050 LEDS
AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1831.0 lumens
Efficiency: N/A
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858553

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2000K

Luminous Intensity Polar Plot





TEST NUMBER: P858553

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	144992
5°	145546
10°	145981
15°	145998
20°	145198
25°	141789
30°	132525
35°	114762
40°	89649
45°	64319
50°	41780
55°	25017
60°	14644
65°	9389
70°	6250
75°	4699
80°	3537
85°	0



TEST NUMBER: P858553

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.4	6.1
10°-20°	323.8	17.7
20°-30°	477.9	26.1
30°-40°	471.6	25.8
40°-50°	288.6	15.8
50°-60°	110.6	6.0
60°-70°	34.6	1.9
70°-80°	10.1	0.6
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	914.1	49.9
0°-40°	1385.7	75.7
0°-60°	1784.9	97.5
0°-90°	1831.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1831.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1180	
5°	1180	112
15°	1148	324
25°	1046	478
35°	765	472
45°	370	289
55°	117	111
65°	32	35
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P858553

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1180.2
2.5°	1182.7
5°	1180.2
7.5°	1177.7
10°	1170.2
12.5°	1160.3
15°	1147.9
17.5°	1132.9
20°	1110.6
22.5°	1085.8
25°	1046.0
27.5°	996.3
30°	934.2
32.5°	857.2
35°	765.2
37.5°	663.3
40°	559.0
42.5°	462.1
45°	370.2
47.5°	288.2
50°	218.6
52.5°	161.5
55°	116.8
57.5°	82.0
60°	59.6
62.5°	44.8
65°	32.3
67.5°	24.9
70°	17.4
72.5°	12.4
75°	9.9
77.5°	5.0
80°	5.0
82.5°	2.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)