

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858565

Luminaire Tested: **LD4C25W2N2765D010 4LBMH_2700K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858565
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2765D010 4LBMH_2700K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1712.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858565

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858565

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	208556
5°	205517
10°	196941
15°	185999
20°	173620
25°	157608
30°	131588
35°	95325
40°	59675
45°	34105
50°	17794
55°	9960
60°	6339
65°	3750
70°	2802
75°	1234
80°	1839
85°	0



TEST NUMBER: P858565

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.2	9.1
10°-20°	409.8	23.9
20°-30°	526.6	30.8
30°-40°	396.2	23.1
40°-50°	159.1	9.3
50°-60°	45.2	2.6
60°-70°	14.3	0.8
70°-80°	4.1	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1092.6	63.8
0°-40°	1488.9	87.0
0°-60°	1693.2	98.9
0°-90°	1712.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1712.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1698	
5°	1666	156
15°	1462	410
25°	1163	527
35°	636	396
45°	196	159
55°	46	45
65°	13	14
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P858565

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1697.6
2.5°	1687.2
5°	1666.5
7.5°	1627.8
10°	1578.7
12.5°	1519.3
15°	1462.4
17.5°	1397.8
20°	1328.0
22.5°	1253.2
25°	1162.7
27.5°	1054.2
30°	927.6
32.5°	785.4
35°	635.6
37.5°	496.1
40°	372.1
42.5°	273.9
45°	196.3
47.5°	134.4
50°	93.1
52.5°	64.6
55°	46.5
57.5°	33.6
60°	25.8
62.5°	18.1
65°	12.9
67.5°	10.3
70°	7.8
72.5°	5.2
75°	2.6
77.5°	2.6
80°	2.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)