

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858087

Luminaire Tested: **LX4C40D010 EX4C409030 4LBMDLI**

Issue Date: 2/18/2022



Test Information

Test Method: LM-79-08
Report Number: P858087
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-8)
Test Lab: INNOVATION CENTER
Issue Date: 2/18/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409030 4LBMDLI
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LRMD45 TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3889.5 lumens
Efficiency: N/A
Efficacy: 59.8 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.82
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858087

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P858087

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	111	109	107		111	109	107	105		105	103	102		101	100	99		98	97	96
2	109	104	100	97		107	102	99	96		99	96	94		96	94	92		94	92	90
3	104	98	93	89		102	96	92	89		94	90	87		91	88	86		89	87	85
4	99	92	87	83		97	91	86	82		89	85	81		87	83	80		85	82	79
5	94	87	81	77		93	86	81	77		84	79	76		82	78	75		81	77	75
6	90	82	76	72		89	81	76	72		80	75	71		78	74	71		77	73	70
7	86	77	72	68		85	77	71	68		75	71	67		74	70	67		73	69	67
8	82	73	68	64		81	73	67	64		72	67	63		71	66	63		70	66	63
9	79	70	64	60		78	69	64	60		68	63	60		67	63	60		66	63	60
10	75	66	61	57		74	66	61	57		65	60	57		64	60	57		63	59	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	627609
5°	648986
10°	655579
15°	590543
20°	490777
25°	385013
30°	281774
35°	145612
40°	69153
45°	24341
50°	5504
55°	3577
60°	2506
65°	1860
70°	1365
75°	854
80°	637
85°	0



TEST NUMBER: P858087

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	502.6	12.9
10°-20°	1278.9	32.9
20°-30°	1294.1	33.3
30°-40°	659.7	17.0
40°-50°	129.3	3.3
50°-60°	15.7	0.4
60°-70°	6.5	0.2
70°-80°	2.3	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3075.6	79.1
0°-40°	3735.3	96.0
0°-60°	3880.3	99.8
0°-90°	3889.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3889.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5109	
5°	5262	503
15°	4643	1279
25°	2840	1294
35°	971	660
45°	140	129
55°	17	16
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P858087

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5108.6
2.5°	5155.9
5°	5262.5
7.5°	5323.8
10°	5255.2
12.5°	5024.2
15°	4643.1
17.5°	4193.3
20°	3753.9
22.5°	3298.5
25°	2840.3
27.5°	2384.1
30°	1986.3
32.5°	1496.7
35°	970.9
37.5°	650.1
40°	431.2
42.5°	270.8
45°	140.1
47.5°	50.0
50°	28.8
52.5°	21.3
55°	16.7
57.5°	13.0
60°	10.2
62.5°	8.3
65°	6.4
67.5°	4.7
70°	3.8
72.5°	2.8
75°	1.8
77.5°	1.8
80°	0.9
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)