

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858089

Luminaire Tested: **LX4C40D010 EX4C409030 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P858089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409030 4LBMLI
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4417.0 lumens
Efficiency: N/A
Efficacy: 68.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858089

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P858089

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1396488
5°	1256684
10°	974200
15°	705126
20°	488241
25°	355937
30°	258623
35°	153036
40°	64374
45°	20067
50°	2580
55°	1456
60°	1671
65°	1977
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858089

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	895.8	20.3
10°-20°	1533.6	34.7
20°-30°	1218.8	27.6
30°-40°	645.2	14.6
40°-50°	111.1	2.5
50°-60°	8.3	0.2
60°-70°	4.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3648.2	82.6
0°-40°	4293.4	97.2
0°-60°	4412.8	99.9
0°-90°	4417.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4417.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11367	
5°	10190	896
15°	5544	1534
25°	2626	1219
35°	1020	645
45°	116	111
55°	7	8
65°	7	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858089

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11367.1
2.5°	11074.5
5°	10190.2
7.5°	9033.9
10°	7809.3
12.5°	6625.7
15°	5544.0
17.5°	4537.2
20°	3734.5
22.5°	3122.3
25°	2625.8
27.5°	2224.4
30°	1823.1
32.5°	1414.9
35°	1020.4
37.5°	673.6
40°	401.4
42.5°	231.4
45°	115.5
47.5°	40.8
50°	13.5
52.5°	13.5
55°	6.8
57.5°	6.8
60°	6.8
62.5°	6.8
65°	6.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)