

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858575

Luminaire Tested: **LD4C25W2N2765D010 4LBMLI_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858575
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2765D010 4LBMLI_5000K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBMLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2464.0 lumens
Efficiency: N/A
Efficacy: 73.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858575

CATALOG NUMBER: LD4C25W2N2765D010 4LBMLI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858575

CATALOG NUMBER: LD4C25W2N2765D010 4LBMLI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	477200
5°	469095
10°	431019
15°	360957
20°	289192
25°	232353
30°	172969
35°	98819
40°	46380
45°	19685
50°	6269
55°	3191
60°	2187
65°	1744
70°	1078
75°	0
80°	0
85°	0



TEST NUMBER: P858575

CATALOG NUMBER: LD4C25W2N2765D010 4LBMLI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	351.7	14.3
10°-20°	786.3	31.9
20°-30°	781.7	31.7
30°-40°	425.7	17.3
40°-50°	98.4	4.0
50°-60°	13.8	0.6
60°-70°	5.2	0.2
70°-80°	1.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1919.7	77.9
0°-40°	2345.4	95.2
0°-60°	2457.7	99.7
0°-90°	2464.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2464.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3884	
5°	3804	352
15°	2838	786
25°	1714	782
35°	659	426
45°	113	98
55°	15	14
65°	6	5
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P858575

CATALOG NUMBER: LD4C25W2N2765D010 4LBMLI_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	3884.3
2.5°	3875.4
5°	3803.8
7.5°	3657.8
10°	3455.1
12.5°	3157.0
15°	2838.0
17.5°	2522.0
20°	2212.0
22.5°	1958.6
25°	1714.1
27.5°	1481.6
30°	1219.3
32.5°	927.2
35°	658.9
37.5°	444.1
40°	289.2
42.5°	181.8
45°	113.3
47.5°	65.6
50°	32.8
52.5°	17.9
55°	14.9
57.5°	8.9
60°	8.9
62.5°	6.0
65°	6.0
67.5°	3.0
70°	3.0
72.5°	3.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)