

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858070

Luminaire Tested: **LX4C40D010 EX4C409030 4LBNH**

Issue Date: 2/8/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P858070  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/8/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX4C40D010 EX4C409030 4LBNH  
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 4LBN TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver:

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2892.2 lumens  
Efficiency: N/A  
Efficacy: 44.5 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 65  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P858070

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

### Luminous Intensity Polar Plot





TEST NUMBER: P858070

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 96  | 106 | 101 | 98  | 94  | 98  | 95  | 92  |  | 95  | 93  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 95  | 90  | 86  | 92  | 88  | 85  |  | 90  | 86  | 84  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 83  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 73  | 81  | 76  | 73  |  | 80  | 75  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 72  | 68  | 77  | 72  | 68  |  | 75  | 71  | 67  |  | 74  |
| 7   | 83  | 74  | 68  | 64  | 82  | 73  | 68  | 64  | 72  | 67  | 63  |  | 71  | 66  | 63  |  | 70  |
| 8   | 79  | 70  | 64  | 60  | 78  | 69  | 64  | 60  | 68  | 63  | 59  |  | 67  | 63  | 59  |  | 66  |
| 9   | 76  | 66  | 60  | 56  | 74  | 65  | 60  | 56  | 65  | 59  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 72  | 62  | 57  | 53  | 71  | 62  | 56  | 53  | 61  | 56  | 53  |  | 60  | 56  | 52  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 446130 |
| 5°  | 436205 |
| 10° | 403313 |
| 15° | 361886 |
| 20° | 318556 |
| 25° | 274158 |
| 30° | 220775 |
| 35° | 146962 |
| 40° | 76450  |
| 45° | 34609  |
| 50° | 15003  |
| 55° | 10067  |
| 60° | 6438   |
| 65° | 4593   |
| 70° | 3772   |
| 75° | 2516   |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P858070

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 327.6  | 11.3      |
| 10°-20°   | 794.7  | 27.5      |
| 20°-30°   | 922.7  | 31.9      |
| 30°-40°   | 611.0  | 21.1      |
| 40°-50°   | 171.4  | 5.9       |
| 50°-60°   | 43.0   | 1.5       |
| 60°-70°   | 16.2   | 0.6       |
| 70°-80°   | 5.6    | 0.2       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2045.0 | 70.7      |
| 0°-40°    | 2656.1 | 91.8      |
| 0°-60°    | 2870.5 | 99.2      |
| 0°-90°    | 2892.2 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2892.2 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3631 |      |
| 5°  | 3537 | 328  |
| 15° | 2845 | 795  |
| 25° | 2022 | 923  |
| 35° | 980  | 611  |
| 45° | 199  | 171  |
| 55° | 47   | 43   |
| 65° | 16   | 16   |
| 75° | 5    | 6    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P858070

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBNH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3631.4 |
| 2.5°  | 3615.6 |
| 5°    | 3537.1 |
| 7.5°  | 3400.7 |
| 10°   | 3233.0 |
| 12.5° | 3044.3 |
| 15°   | 2845.3 |
| 17.5° | 2651.3 |
| 20°   | 2436.6 |
| 22.5° | 2237.4 |
| 25°   | 2022.5 |
| 27.5° | 1818.3 |
| 30°   | 1556.3 |
| 32.5° | 1278.6 |
| 35°   | 979.9  |
| 37.5° | 702.2  |
| 40°   | 476.7  |
| 42.5° | 309.0  |
| 45°   | 199.2  |
| 47.5° | 120.6  |
| 50°   | 78.5   |
| 52.5° | 57.6   |
| 55°   | 47.0   |
| 57.5° | 36.8   |
| 60°   | 26.2   |
| 62.5° | 21.0   |
| 65°   | 15.8   |
| 67.5° | 10.5   |
| 70°   | 10.5   |
| 72.5° | 5.3    |
| 75°   | 5.3    |
| 77.5° | 5.3    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)