

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858076

Luminaire Tested: **LX4C40D010 EX4C409030 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P858076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C40D010 EX4C409030 4LBWLI
Description: 4 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH, DIM TO WARM
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4582.8 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 65
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858076

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWLI

Luminous Intensity Polar Plot






TEST NUMBER: P858076

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):



TEST NUMBER: P858076

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	274.6	6.0
10°-20°	866.6	18.9
20°-30°	1351.8	29.5
30°-40°	1315.3	28.7
40°-50°	657.0	14.3
50°-60°	101.7	2.2
60°-70°	12.3	0.3
70°-80°	3.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2493.0	54.4
0°-40°	3808.3	83.1
0°-60°	4567.0	99.7
0°-90°	4582.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4582.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2808	
5°	2845	275
15°	3060	867
25°	2971	1352
35°	2136	1315
45°	824	657
55°	84	102
65°	10	12
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P858076

CATALOG NUMBER: LX4C40D010 EX4C409030 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2807.8
2.5°	2818.3
5°	2844.6
7.5°	2886.6
10°	2939.2
12.5°	3007.2
15°	3059.8
17.5°	3101.9
20°	3107.1
22.5°	3070.4
25°	2970.7
27.5°	2823.6
30°	2639.9
32.5°	2409.1
35°	2136.1
37.5°	1836.9
40°	1522.0
42.5°	1186.2
45°	824.1
47.5°	530.0
50°	320.0
52.5°	173.2
55°	84.1
57.5°	36.8
60°	21.0
62.5°	15.8
65°	10.5
67.5°	10.5
70°	5.3
72.5°	5.3
75°	5.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)