

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858625

Luminaire Tested: **LD4C30W2N2050D010 4LBNLI_2000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858625
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2050D010 4LBNLI_2000K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2000K, W2N2050 LEDS
AND 4LBNLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2084.0 lumens
Efficiency: N/A
Efficacy: 52.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858625

CATALOG NUMBER: LD4C30W2N2050D010 4LBNLI_2000K

Luminous Intensity Polar Plot





TEST NUMBER: P858625

CATALOG NUMBER: LD4C30W2N2050D010 4LBNLI_2000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	658863
5°	592911
10°	459637
15°	332684
20°	230360
25°	167938
30°	122027
35°	72199
40°	30375
45°	9469
50°	1223
55°	685
60°	786
65°	930
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858625

CATALOG NUMBER: LD4C30W2N2050D010 4LBNLI_2000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	422.6	20.3
10°-20°	723.6	34.7
20°-30°	575.1	27.6
30°-40°	304.4	14.6
40°-50°	52.4	2.5
50°-60°	3.9	0.2
60°-70°	2.0	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1721.3	82.6
0°-40°	2025.7	97.2
0°-60°	2082.0	99.9
0°-90°	2084.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2084.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5363	
5°	4808	423
15°	2616	724
25°	1239	575
35°	481	304
45°	54	52
55°	3	4
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858625

CATALOG NUMBER: LD4C30W2N2050D010 4LBNLI_2000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	5363.0
2.5°	5224.9
5°	4807.8
7.5°	4262.2
10°	3684.5
12.5°	3126.1
15°	2615.7
17.5°	2140.7
20°	1762.0
22.5°	1473.1
25°	1238.9
27.5°	1049.5
30°	860.2
32.5°	667.6
35°	481.4
37.5°	317.8
40°	189.4
42.5°	109.1
45°	54.5
47.5°	19.3
50°	6.4
52.5°	6.4
55°	3.2
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)