

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858476

Luminaire Tested: **LD4C20W2N2050D010 4LBWLI_2700K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858476
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20W2N2050D010 4LBWLI_2700K
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2050 LEDS
AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1769.0 lumens
Efficiency: N/A
Efficacy: 69.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 25.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858476

CATALOG NUMBER: LD4C20W2N2050D010 4LBWLI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858476

CATALOG NUMBER: LD4C20W2N2050D010 4LBWLI_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133161
5°	135421
10°	141540
15°	150221
20°	156807
25°	155440
30°	144554
35°	123671
40°	94220
45°	55267
50°	23623
55°	6961
60°	1990
65°	1192
70°	718
75°	949
80°	0
85°	0



TEST NUMBER: P858476

CATALOG NUMBER: LD4C20W2N2050D010 4LBWLI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.0	6.0
10°-20°	334.5	18.9
20°-30°	521.8	29.5
30°-40°	507.7	28.7
40°-50°	253.6	14.3
50°-60°	39.3	2.2
60°-70°	4.8	0.3
70°-80°	1.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	962.3	54.4
0°-40°	1470.0	83.1
0°-60°	1762.9	99.7
0°-90°	1769.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1769.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1084	
5°	1098	106
15°	1181	335
25°	1147	522
35°	825	508
45°	318	254
55°	32	39
65°	4	5
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P858476

CATALOG NUMBER: LD4C20W2N2050D010 4LBWLI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1083.9
2.5°	1087.9
5°	1098.1
7.5°	1114.3
10°	1134.6
12.5°	1160.8
15°	1181.1
17.5°	1197.4
20°	1199.4
22.5°	1185.2
25°	1146.7
27.5°	1089.9
30°	1019.0
32.5°	930.0
35°	824.6
37.5°	709.0
40°	587.5
42.5°	457.9
45°	318.1
47.5°	204.6
50°	123.6
52.5°	66.8
55°	32.5
57.5°	14.2
60°	8.1
62.5°	6.1
65°	4.1
67.5°	4.1
70°	2.0
72.5°	2.0
75°	2.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)