

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858654

Luminaire Tested: **LD4C30W2N2765D010 4LBMH_6500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858654
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2765D010 4LBMH_6500K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 6500K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2636.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858654

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P858654

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	321114
5°	316446
10°	303227
15°	286400
20°	267333
25°	242682
30°	202617
35°	146782
40°	91878
45°	52522
50°	27388
55°	15336
60°	9779
65°	5785
70°	4274
75°	1899
80°	2830
85°	0



TEST NUMBER: P858654

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	240.5	9.1
10°-20°	631.0	23.9
20°-30°	810.9	30.8
30°-40°	610.1	23.1
40°-50°	245.0	9.3
50°-60°	69.6	2.6
60°-70°	22.1	0.8
70°-80°	6.3	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1682.4	63.8
0°-40°	2292.5	87.0
0°-60°	2607.1	98.9
0°-90°	2636.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2636.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2614	
5°	2566	241
15°	2252	631
25°	1790	811
35°	979	610
45°	302	245
55°	72	70
65°	20	22
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P858654

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2613.8
2.5°	2597.8
5°	2566.0
7.5°	2506.3
10°	2430.7
12.5°	2339.3
15°	2251.8
17.5°	2152.3
20°	2044.8
22.5°	1929.6
25°	1790.3
27.5°	1623.1
30°	1428.3
32.5°	1209.4
35°	978.7
37.5°	763.8
40°	572.9
42.5°	421.7
45°	302.3
47.5°	207.0
50°	143.3
52.5°	99.5
55°	71.6
57.5°	51.7
60°	39.8
62.5°	27.9
65°	19.9
67.5°	15.9
70°	11.9
72.5°	8.0
75°	4.0
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)