

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858485

Luminaire Tested: **LD4C20W2N2765D010 4LBMH_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858485
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20W2N2765D010 4LBMH_5000K
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1550.0 lumens
Efficiency: N/A
Efficacy: 61.0 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 25.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858485

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858485

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188814
5°	186069
10°	178303
15°	168409
20°	157199
25°	142697
30°	119133
35°	86311
40°	54030
45°	30891
50°	16093
55°	9017
60°	5750
65°	3401
70°	2514
75°	1092
80°	1627
85°	0



TEST NUMBER: P858485

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.4	9.1
10°-20°	371.0	23.9
20°-30°	476.8	30.8
30°-40°	358.7	23.1
40°-50°	144.1	9.3
50°-60°	40.9	2.6
60°-70°	13.0	0.8
70°-80°	3.7	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.2	63.8
0°-40°	1348.0	87.0
0°-60°	1533.0	98.9
0°-90°	1550.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1550.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1537	
5°	1509	141
15°	1324	371
25°	1053	477
35°	576	359
45°	178	144
55°	42	41
65°	12	13
75°	2	4
85°	0	0
90°	0	



TEST NUMBER: P858485

CATALOG NUMBER: LD4C20W2N2765D010 4LBMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1536.9
2.5°	1527.6
5°	1508.8
7.5°	1473.7
10°	1429.3
12.5°	1375.5
15°	1324.1
17.5°	1265.6
20°	1202.4
22.5°	1134.6
25°	1052.7
27.5°	954.4
30°	839.8
32.5°	711.1
35°	575.5
37.5°	449.1
40°	336.9
42.5°	248.0
45°	177.8
47.5°	121.7
50°	84.2
52.5°	58.5
55°	42.1
57.5°	30.4
60°	23.4
62.5°	16.4
65°	11.7
67.5°	9.4
70°	7.0
72.5°	4.7
75°	2.3
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)