

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858666

Luminaire Tested: **LD4C30W2N2765D010 4LBNH_6500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2765D010 4LBNH_6500K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 6500K, W2N2765 LEDS
AND 4LBNH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2190.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858666

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P858666

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344899
5°	336363
10°	310362
15°	274775
20°	238584
25°	204076
30°	168245
35°	110788
40°	59563
45°	26374
50°	10684
55°	7711
60°	4890
65°	3488
70°	2874
75°	1899
80°	2830
85°	0



TEST NUMBER: P858666

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.5	11.5
10°-20°	602.0	27.5
20°-30°	689.7	31.5
30°-40°	463.4	21.2
40°-50°	132.4	6.0
50°-60°	32.4	1.5
60°-70°	12.3	0.6
70°-80°	4.8	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1544.2	70.5
0°-40°	2007.6	91.7
0°-60°	2172.4	99.2
0°-90°	2190.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2190.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2807	
5°	2728	252
15°	2160	602
25°	1506	690
35°	739	463
45°	152	132
55°	36	32
65°	12	12
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P858666

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2807.4
2.5°	2787.4
5°	2727.5
7.5°	2619.6
10°	2487.9
12.5°	2320.1
15°	2160.4
17.5°	1992.7
20°	1824.9
22.5°	1665.3
25°	1505.5
27.5°	1357.7
30°	1186.0
32.5°	958.4
35°	738.7
37.5°	539.1
40°	371.4
42.5°	243.6
45°	151.8
47.5°	91.8
50°	55.9
52.5°	43.9
55°	36.0
57.5°	28.0
60°	19.9
62.5°	15.9
65°	12.0
67.5°	8.0
70°	8.0
72.5°	4.0
75°	4.0
77.5°	4.0
80°	4.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)