

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858494

Luminaire Tested: **LD4C20W2N2765D010 4LBNH_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858494
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C20W2N2765D010 4LBNH_3000K
Description: 4 INCH 2000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2765 LEDS
AND 4LBNH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1302.0 lumens
Efficiency: N/A
Efficacy: 51.3 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 25.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858494

CATALOG NUMBER: LD4C20W2N2765D010 4LBNH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858494

CATALOG NUMBER: LD4C20W2N2765D010 4LBNH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	111	108	106	111	109	106	104	104	103	101		101	99	98		97
2	108	103	99	96	106	101	98	94	98	95	92		95	93	90		92
3	102	96	91	87	100	95	90	86	92	88	85		90	86	84		87
4	97	90	84	80	95	89	83	79	86	82	78		84	81	78		83
5	92	84	78	74	91	83	78	73	81	76	73		80	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	83	74	68	64	82	73	68	64	72	67	63		71	66	63		70
8	79	70	64	60	78	69	64	60	68	63	59		67	63	59		66
9	76	66	60	56	75	66	60	56	65	59	56		64	59	56		63
10	72	62	57	53	71	62	57	53	61	56	53		60	56	52		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	205042
5°	199968
10°	184516
15°	163359
20°	141838
25°	121321
30°	100025
35°	65870
40°	35411
45°	15671
50°	6364
55°	4584
60°	2924
65°	2093
70°	1724
75°	1139
80°	1698
85°	0



TEST NUMBER: P858494

CATALOG NUMBER: LD4C20W2N2765D010 4LBNH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.1	11.5
10°-20°	357.9	27.5
20°-30°	410.0	31.5
30°-40°	275.5	21.2
40°-50°	78.7	6.0
50°-60°	19.3	1.5
60°-70°	7.4	0.6
70°-80°	2.9	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	918.0	70.5
0°-40°	1193.5	91.7
0°-60°	1291.5	99.2
0°-90°	1302.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1302.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1669	
5°	1622	150
15°	1284	358
25°	895	410
35°	439	276
45°	90	79
55°	21	19
65°	7	7
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P858494

CATALOG NUMBER: LD4C20W2N2765D010 4LBNH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1669.0
2.5°	1657.2
5°	1621.5
7.5°	1557.4
10°	1479.1
12.5°	1379.3
15°	1284.4
17.5°	1184.7
20°	1084.9
22.5°	990.0
25°	895.0
27.5°	807.2
30°	705.1
32.5°	569.8
35°	439.2
37.5°	320.5
40°	220.8
42.5°	144.8
45°	90.2
47.5°	54.6
50°	33.3
52.5°	26.1
55°	21.4
57.5°	16.6
60°	11.9
62.5°	9.5
65°	7.2
67.5°	4.8
70°	4.8
72.5°	2.4
75°	2.4
77.5°	2.4
80°	2.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)