

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858721

Luminaire Tested: **LD4C35W2N2050D010 4LBWH_2000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858721
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2050D010 4LBWH_2000K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2000K, W2N2050 LEDS
AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2620.0 lumens
Efficiency: N/A
Efficacy: 49.6 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858721

CATALOG NUMBER: LD4C35W2N2050D010 4LBWH_2000K

Luminous Intensity Polar Plot





TEST NUMBER: P858721

CATALOG NUMBER: LD4C35W2N2050D010 4LBWH_2000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	207463
5°	208255
10°	208892
15°	208905
20°	207756
25°	202883
30°	189637
35°	164209
40°	128283
45°	92048
50°	59784
55°	35791
60°	20934
65°	13459
70°	8944
75°	6740
80°	5023
85°	0



TEST NUMBER: P858721

CATALOG NUMBER: LD4C35W2N2050D010 4LBWH_2000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.8	6.1
10°-20°	463.4	17.7
20°-30°	683.8	26.1
30°-40°	674.8	25.8
40°-50°	413.0	15.8
50°-60°	158.3	6.0
60°-70°	49.5	1.9
70°-80°	14.5	0.6
80°-90°	1.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1308.0	49.9
0°-40°	1982.8	75.7
0°-60°	2554.1	97.5
0°-90°	2620.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2620.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1689	
5°	1689	161
15°	1642	463
25°	1497	684
35°	1095	675
45°	530	413
55°	167	158
65°	46	50
75°	14	14
85°	0	2
90°	0	



TEST NUMBER: P858721

CATALOG NUMBER: LD4C35W2N2050D010 4LBWH_2000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1688.7
2.5°	1692.3
5°	1688.7
7.5°	1685.2
10°	1674.5
12.5°	1660.3
15°	1642.5
17.5°	1621.1
20°	1589.1
22.5°	1553.7
25°	1496.7
27.5°	1425.6
30°	1336.8
32.5°	1226.6
35°	1094.9
37.5°	949.2
40°	799.9
42.5°	661.3
45°	529.8
47.5°	412.3
50°	312.8
52.5°	231.2
55°	167.1
57.5°	117.3
60°	85.2
62.5°	64.1
65°	46.3
67.5°	35.6
70°	24.9
72.5°	17.8
75°	14.2
77.5°	7.1
80°	7.1
82.5°	3.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)