

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858752

Luminaire Tested: **LD4C35W2N2765D010 4LBNLI_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858752
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBNLI_3000K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2765 LEDS
AND 4LBNLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2797.0 lumens
Efficiency: N/A
Efficacy: 53.0 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858752

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858752

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	884287
5°	795765
10°	616895
15°	446504
20°	309169
25°	225385
30°	163762
35°	96915
40°	40751
45°	12700
50°	1644
55°	921
60°	1057
65°	1250
70°	0
75°	0
80°	0
85°	0

TEST NUMBER: P858752

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	567.2	20.3
10°-20°	971.1	34.7
20°-30°	771.8	27.6
30°-40°	408.6	14.6
40°-50°	70.4	2.5
50°-60°	5.3	0.2
60°-70°	2.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2310.1	82.6
0°-40°	2718.7	97.2
0°-60°	2794.3	99.9
0°-90°	2797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2797.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7198	
5°	6453	567
15°	3511	971
25°	1663	772
35°	646	409
45°	73	70
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858752

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	7197.9
2.5°	7012.6
5°	6452.7
7.5°	5720.5
10°	4945.1
12.5°	4195.6
15°	3510.6
17.5°	2873.1
20°	2364.8
22.5°	1977.1
25°	1662.7
27.5°	1408.6
30°	1154.4
32.5°	896.0
35°	646.2
37.5°	426.5
40°	254.1
42.5°	146.5
45°	73.1
47.5°	25.9
50°	8.6
52.5°	8.6
55°	4.3
57.5°	4.3
60°	4.3
62.5°	4.3
65°	4.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)