

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858754

Luminaire Tested: **LD4C35W2N2765D010 4LBNLI_4000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBNLI_4000K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, W2N2765 LEDS
AND 4LBNLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2665.0 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858754

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P858754

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90		
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85		
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81		
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77		
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73		
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69		
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66		
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63		
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	842554
5°	758213
10°	587778
15°	425429
20°	294579
25°	214758
30°	156045
35°	92340
40°	38843
45°	12110
50°	1567
55°	878
60°	1007
65°	1192
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858754

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	540.5	20.3
10°-20°	925.3	34.7
20°-30°	735.4	27.6
30°-40°	389.3	14.6
40°-50°	67.1	2.5
50°-60°	5.0	0.2
60°-70°	2.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2201.1	82.6
0°-40°	2590.4	97.2
0°-60°	2662.5	99.9
0°-90°	2665.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2665.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6858	
5°	6148	540
15°	3345	925
25°	1584	735
35°	616	389
45°	70	67
55°	4	5
65°	4	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858754

CATALOG NUMBER: LD4C35W2N2765D010 4LBNLI_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	6858.2
2.5°	6681.6
5°	6148.2
7.5°	5450.5
10°	4711.7
12.5°	3997.6
15°	3344.9
17.5°	2737.5
20°	2253.2
22.5°	1883.8
25°	1584.3
27.5°	1342.1
30°	1100.0
32.5°	853.7
35°	615.7
37.5°	406.4
40°	242.2
42.5°	139.6
45°	69.7
47.5°	24.7
50°	8.2
52.5°	8.2
55°	4.1
57.5°	4.1
60°	4.1
62.5°	4.1
65°	4.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)