

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858554

Luminaire Tested: **LD4C25W2N2050D010 4LBWH_2700K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858554
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2050D010 4LBWH_2700K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2050 LEDS
AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1903.0 lumens
Efficiency: N/A
Efficacy: 56.8 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858554

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858554

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150692
5°	151268
10°	151732
15°	151734
20°	150898
25°	147361
30°	137731
35°	119276
40°	93177
45°	66856
50°	43424
55°	26002
60°	15209
65°	9767
70°	6502
75°	4889
80°	3679
85°	0



TEST NUMBER: P858554

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	6.1
10°-20°	336.6	17.7
20°-30°	496.7	26.1
30°-40°	490.1	25.8
40°-50°	299.9	15.8
50°-60°	115.0	6.0
60°-70°	35.9	1.9
70°-80°	10.5	0.6
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	950.0	49.9
0°-40°	1440.2	75.7
0°-60°	1855.1	97.5
0°-90°	1903.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1903.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1227	
5°	1227	117
15°	1193	337
25°	1087	497
35°	795	490
45°	385	300
55°	121	115
65°	34	36
75°	10	11
85°	0	1
90°	0	



TEST NUMBER: P858554

CATALOG NUMBER: LD4C25W2N2050D010 4LBWH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1226.6
2.5°	1229.2
5°	1226.6
7.5°	1224.0
10°	1216.3
12.5°	1205.9
15°	1193.0
17.5°	1177.5
20°	1154.2
22.5°	1128.5
25°	1087.1
27.5°	1035.4
30°	970.9
32.5°	890.9
35°	795.3
37.5°	689.4
40°	581.0
42.5°	480.3
45°	384.8
47.5°	299.5
50°	227.2
52.5°	167.9
55°	121.4
57.5°	85.2
60°	61.9
62.5°	46.5
65°	33.6
67.5°	25.8
70°	18.1
72.5°	12.9
75°	10.3
77.5°	5.2
80°	5.2
82.5°	2.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)