

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858566

Luminaire Tested: **LD4C25W2N2765D010 4LBMH_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2765D010 4LBMH_3000K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1997.0 lumens
Efficiency: N/A
Efficacy: 59.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858566

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858566

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243262
5°	239739
10°	229725
15°	216969
20°	202526
25°	183852
30°	153491
35°	111208
40°	69602
45°	39787
50°	20737
55°	11630
60°	7420
65°	4390
70°	3233
75°	1424
80°	2122
85°	0



TEST NUMBER: P858566

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.2	9.1
10°-20°	478.0	23.9
20°-30°	614.3	30.8
30°-40°	462.2	23.1
40°-50°	185.6	9.3
50°-60°	52.8	2.6
60°-70°	16.7	0.8
70°-80°	4.7	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1274.5	63.8
0°-40°	1736.7	87.0
0°-60°	1975.1	98.9
0°-90°	1997.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1997.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1980	
5°	1944	182
15°	1706	478
25°	1356	614
35°	742	462
45°	229	186
55°	54	53
65°	15	17
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P858566

CATALOG NUMBER: LD4C25W2N2765D010 4LBMH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1980.1
2.5°	1968.1
5°	1944.0
7.5°	1898.7
10°	1841.5
12.5°	1772.2
15°	1705.9
17.5°	1630.5
20°	1549.1
22.5°	1461.8
25°	1356.3
27.5°	1229.6
30°	1082.0
32.5°	916.2
35°	741.5
37.5°	578.6
40°	434.0
42.5°	319.5
45°	229.0
47.5°	156.8
50°	108.5
52.5°	75.4
55°	54.3
57.5°	39.2
60°	30.2
62.5°	21.1
65°	15.1
67.5°	12.1
70°	9.0
72.5°	6.0
75°	3.0
77.5°	3.0
80°	3.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)