

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858771

Luminaire Tested: **LD4C35W2N2765D010 4LBWLI_3500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858771
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBWLI_3500K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, W2N2765 LEDS
AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3695.0 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858771

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P858771

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77		
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70		
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64		
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58		
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54		
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49		
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45		
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	278128
5°	282853
10°	295629
15°	313784
20°	327525
25°	324692
30°	301947
35°	258304
40°	196811
45°	115434
50°	49330
55°	14522
60°	4152
65°	2471
70°	1509
75°	1994
80°	0
85°	0



TEST NUMBER: P858771

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.4	6.0
10°-20°	698.7	18.9
20°-30°	1090.0	29.5
30°-40°	1060.5	28.7
40°-50°	529.7	14.3
50°-60°	82.0	2.2
60°-70°	9.9	0.3
70°-80°	2.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2010.1	54.4
0°-40°	3070.6	83.1
0°-60°	3682.3	99.7
0°-90°	3695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3695.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2264	
5°	2294	221
15°	2467	699
25°	2395	1090
35°	1722	1061
45°	664	530
55°	68	82
65°	8	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P858771

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2263.9
2.5°	2272.4
5°	2293.6
7.5°	2327.5
10°	2369.8
12.5°	2424.7
15°	2467.1
17.5°	2501.0
20°	2505.2
22.5°	2475.6
25°	2395.3
27.5°	2276.6
30°	2128.5
32.5°	1942.5
35°	1722.3
37.5°	1481.0
40°	1227.2
42.5°	956.4
45°	664.4
47.5°	427.4
50°	258.1
52.5°	139.6
55°	67.8
57.5°	29.7
60°	16.9
62.5°	12.7
65°	8.5
67.5°	8.5
70°	4.2
72.5°	4.2
75°	4.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)