

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858774

Luminaire Tested: **LD4C35W2N2765D010 4LBWLI_6500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBWLI_6500K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 6500K, W2N2765 LEDS
AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3843.0 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858774

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P858774

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	289271
5°	294174
10°	307481
15°	326350
20°	340651
25°	337692
30°	314047
35°	268653
40°	204685
45°	120072
50°	51298
55°	15100
60°	4324
65°	2558
70°	1580
75°	2089
80°	0
85°	0



TEST NUMBER: P858774

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	230.3	6.0
10°-20°	726.7	18.9
20°-30°	1133.6	29.5
30°-40°	1103.0	28.7
40°-50°	550.9	14.3
50°-60°	85.3	2.2
60°-70°	10.3	0.3
70°-80°	2.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2090.6	54.4
0°-40°	3193.6	83.1
0°-60°	3829.8	99.7
0°-90°	3843.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3843.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2355	
5°	2385	230
15°	2566	727
25°	2491	1134
35°	1791	1103
45°	691	551
55°	70	85
65°	9	10
75°	4	3
85°	0	0
90°	0	



TEST NUMBER: P858774

CATALOG NUMBER: LD4C35W2N2765D010 4LBWLI_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2354.6
2.5°	2363.4
5°	2385.4
7.5°	2420.7
10°	2464.8
12.5°	2521.8
15°	2565.9
17.5°	2601.2
20°	2605.6
22.5°	2574.7
25°	2491.2
27.5°	2367.8
30°	2213.8
32.5°	2020.3
35°	1791.3
37.5°	1540.3
40°	1276.3
42.5°	994.7
45°	691.1
47.5°	444.5
50°	268.4
52.5°	145.2
55°	70.5
57.5°	30.8
60°	17.6
62.5°	13.2
65°	8.8
67.5°	8.8
70°	4.4
72.5°	4.4
75°	4.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)