

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858602

Luminaire Tested: **LD4C25W2N2765D010 4LBWLI_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858602
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2765D010 4LBWLI_3000K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2765 LEDS
AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2628.9 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858602

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858602

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	107	105		110	108	105	103		104	102	100		100	98	97		96	95	94
2	106	101	97	93		104	99	95	92		96	93	90		93	90	88		90	88	86
3	100	93	87	83		98	92	86	82		89	85	81		86	83	80		84	81	78
4	94	86	79	75		92	84	79	74		82	77	73		80	76	72		78	75	72
5	88	79	72	68		87	78	72	67		76	71	67		74	70	66		73	69	65
6	83	73	66	62		82	72	66	61		71	65	61		69	64	60		68	63	60
7	78	68	61	56		77	67	61	56		66	60	56		64	59	55		63	59	55
8	74	63	56	52		72	62	56	51		61	55	51		60	55	51		59	54	51
9	69	59	52	48		68	58	52	47		57	51	47		56	51	47		55	50	47
10	66	55	48	44		65	54	48	44		53	48	44		53	47	44		52	47	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	197892
5°	201250
10°	210339
15°	223252
20°	233040
25°	231011
30°	214831
35°	183781
40°	140022
45°	82127
50°	35091
55°	10324
60°	2973
65°	1744
70°	1078
75°	1424
80°	0
85°	0



TEST NUMBER: P858602

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.5	6.0
10°-20°	497.1	18.9
20°-30°	775.5	29.5
30°-40°	754.6	28.7
40°-50°	376.9	14.3
50°-60°	58.3	2.2
60°-70°	7.0	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1430.2	54.4
0°-40°	2184.7	83.1
0°-60°	2619.9	99.7
0°-90°	2628.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2628.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1611	
5°	1632	158
15°	1755	497
25°	1704	776
35°	1225	755
45°	473	377
55°	48	58
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P858602

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1610.8
2.5°	1616.8
5°	1631.9
7.5°	1656.0
10°	1686.1
12.5°	1725.2
15°	1755.3
17.5°	1779.5
20°	1782.5
22.5°	1761.4
25°	1704.2
27.5°	1619.8
30°	1514.4
32.5°	1382.1
35°	1225.4
37.5°	1053.8
40°	873.1
42.5°	680.5
45°	472.7
47.5°	304.1
50°	183.6
52.5°	99.3
55°	48.2
57.5°	21.1
60°	12.1
62.5°	9.0
65°	6.0
67.5°	6.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)