

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858605

Luminaire Tested: **LD4C25W2N2765D010 4LBWLI_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858605
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C25W2N2765D010 4LBWLI_5000K
Description: 4 INCH 2500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBWLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2601.0 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 33.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858605

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858605

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10		50	30	10			50	30	10			50
RCR																				
0	119	119	119	119	116	116	116	116		111	111	111			106	106	106			102
1	113	110	107	105	110	108	105	103		104	102	100			100	98	97			96
2	106	101	97	93	104	99	95	92		96	93	90			93	90	88			90
3	100	93	87	83	98	92	86	82		89	85	81			86	83	80			84
4	94	86	79	75	92	84	79	74		82	77	73			80	76	72			78
5	88	79	72	68	87	78	72	67		76	71	67			74	70	66			73
6	83	73	66	62	82	72	66	61		71	65	61			69	64	60			68
7	78	68	61	56	77	67	61	56		66	60	56			64	59	55			63
8	74	63	56	52	72	62	56	51		61	55	51			60	55	51			59
9	69	59	52	48	68	58	52	47		57	51	47			56	51	47			55
10	66	55	48	44	65	54	48	44		53	48	44			53	47	44			52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	195779
5°	199105
10°	208106
15°	220873
20°	230556
25°	228557
30°	212547
35°	181831
40°	138531
45°	81259
50°	34728
55°	10217
60°	2924
65°	1744
70°	1078
75°	1424
80°	0
85°	0



TEST NUMBER: P858605

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.8	6.0
10°-20°	491.8	18.9
20°-30°	767.3	29.5
30°-40°	746.5	28.7
40°-50°	372.9	14.3
50°-60°	57.7	2.2
60°-70°	7.0	0.3
70°-80°	2.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1414.9	54.4
0°-40°	2161.5	83.1
0°-60°	2592.1	99.7
0°-90°	2601.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2601.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1594	
5°	1614	156
15°	1737	492
25°	1686	767
35°	1212	747
45°	468	373
55°	48	58
65°	6	7
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P858605

CATALOG NUMBER: LD4C25W2N2765D010 4LBWLI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1593.6
2.5°	1599.6
5°	1614.5
7.5°	1638.4
10°	1668.2
12.5°	1706.8
15°	1736.6
17.5°	1760.5
20°	1763.5
22.5°	1742.6
25°	1686.1
27.5°	1602.6
30°	1498.3
32.5°	1367.4
35°	1212.4
37.5°	1042.5
40°	863.8
42.5°	673.2
45°	467.7
47.5°	300.8
50°	181.7
52.5°	98.3
55°	47.7
57.5°	20.9
60°	11.9
62.5°	8.9
65°	6.0
67.5°	6.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)