

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859076

Luminaire Tested: **LX4C55D010 EX4C559027 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C55D010 EX4C559027 4LBWLI
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5618.0 lumens
Efficiency: N/A
Efficacy: 87.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859076

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBWLI

Luminous Intensity Polar Plot





TEST NUMBER: P859076

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859076

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBWLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	336.6	6.0
10°-20°	1062.3	18.9
20°-30°	1657.2	29.5
30°-40°	1612.5	28.7
40°-50°	805.4	14.3
50°-60°	124.7	2.2
60°-70°	15.1	0.3
70°-80°	4.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3056.1	54.4
0°-40°	4668.6	83.1
0°-60°	5598.7	99.7
0°-90°	5618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5618.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3442	
5°	3487	337
15°	3751	1062
25°	3642	1657
35°	2619	1612
45°	1010	805
55°	103	125
65°	13	15
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P859076

CATALOG NUMBER: LX4C55D010 EX4C559027 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3442.1
2.5°	3455.0
5°	3487.2
7.5°	3538.8
10°	3603.2
12.5°	3686.6
15°	3751.0
17.5°	3802.6
20°	3809.0
22.5°	3763.9
25°	3641.8
27.5°	3461.4
30°	3236.3
32.5°	2953.4
35°	2618.7
37.5°	2251.8
40°	1865.9
42.5°	1454.2
45°	1010.2
47.5°	649.8
50°	392.4
52.5°	212.3
55°	103.1
57.5°	45.1
60°	25.8
62.5°	19.3
65°	12.9
67.5°	12.9
70°	6.4
72.5°	6.4
75°	6.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)