

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858615

Luminaire Tested: **LD4C30W2N2050D010 4LBMLI_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2050D010 4LBMLI_3000K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2050 LEDS
AND 4LBMLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3219.0 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858615

CATALOG NUMBER: LD4C30W2N2050D010 4LBMLI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858615

CATALOG NUMBER: LD4C30W2N2050D010 4LBMLI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	623432
5°	612828
10°	563091
15°	471560
20°	377793
25°	303559
30°	225967
35°	129100
40°	60589
45°	25731
50°	8199
55°	4177
60°	2875
65°	2267
70°	1401
75°	0
80°	0
85°	0



TEST NUMBER: P858615

CATALOG NUMBER: LD4C30W2N2050D010 4LBMLI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	459.5	14.3
10°-20°	1027.2	31.9
20°-30°	1021.3	31.7
30°-40°	556.2	17.3
40°-50°	128.6	4.0
50°-60°	18.1	0.6
60°-70°	6.7	0.2
70°-80°	1.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2507.9	77.9
0°-40°	3064.1	95.2
0°-60°	3210.8	99.7
0°-90°	3219.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3219.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5075	
5°	4969	459
15°	3708	1027
25°	2239	1021
35°	861	556
45°	148	129
55°	20	18
65°	8	7
75°	0	2
85°	0	0
90°	0	



TEST NUMBER: P858615

CATALOG NUMBER: LD4C30W2N2050D010 4LBMLI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5074.6
2.5°	5062.9
5°	4969.3
7.5°	4778.6
10°	4513.8
12.5°	4124.4
15°	3707.6
17.5°	3294.8
20°	2889.7
22.5°	2558.7
25°	2239.4
27.5°	1935.6
30°	1592.9
32.5°	1211.3
35°	860.8
37.5°	580.2
40°	377.8
42.5°	237.5
45°	148.1
47.5°	85.7
50°	42.9
52.5°	23.4
55°	19.5
57.5°	11.7
60°	11.7
62.5°	7.8
65°	7.8
67.5°	3.9
70°	3.9
72.5°	3.9
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)