

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859084

Luminaire Tested: **LD4C55D010 EU4559030 4LBMLI**

Issue Date: 7/19/2024



Test Information

Test Method: LM-79-08
Report Number: P859084
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208178)
Test Lab: INNOVATION CENTER
Issue Date: 7/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C55D010 EU4559030 4LBMLI
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5535.0 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.76
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859084

CATALOG NUMBER: LD4C55D010 EU4559030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859084

CATALOG NUMBER: LD4C55D010 EU4559030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	71		78	74	71		77
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73
8	82	73	68	64	81	73	67	64	72	67	64		71	66	63		70
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1071970
5°	1053756
10°	968224
15°	810844
20°	649611
25°	521964
30°	388552
35°	221965
40°	104179
45°	44234
50°	14086
55°	7175
60°	4939
65°	3895
70°	2407
75°	0
80°	0
85°	0



TEST NUMBER: P859084

CATALOG NUMBER: LD4C55D010 EU4559030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	790.0	14.3
10°-20°	1766.3	31.9
20°-30°	1756.1	31.7
30°-40°	956.3	17.3
40°-50°	221.0	4.0
50°-60°	31.1	0.6
60°-70°	11.6	0.2
70°-80°	2.6	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4312.3	77.9
0°-40°	5268.6	95.2
0°-60°	5520.8	99.7
0°-90°	5535.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5535.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8726	
5°	8545	790
15°	6375	1766
25°	3851	1756
35°	1480	956
45°	255	221
55°	34	31
65°	13	12
75°	0	3
85°	0	0
90°	0	



TEST NUMBER: P859084

CATALOG NUMBER: LD4C55D010 EU4559030 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	8725.6
2.5°	8705.5
5°	8544.7
7.5°	8216.7
10°	7761.4
12.5°	7091.7
15°	6375.2
17.5°	5665.3
20°	4968.8
22.5°	4399.6
25°	3850.6
27.5°	3328.3
30°	2739.0
32.5°	2082.7
35°	1480.0
37.5°	997.7
40°	649.6
42.5°	408.4
45°	254.6
47.5°	147.4
50°	73.7
52.5°	40.2
55°	33.5
57.5°	20.1
60°	20.1
62.5°	13.4
65°	13.4
67.5°	6.7
70°	6.7
72.5°	6.7
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)