

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859089

Luminaire Tested: **LX4C55D010 EX4C559030 4LBMH**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859089
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C55D010 EX4C559030 4LBMH
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4436.0 lumens
Efficiency: N/A
Efficacy: 69.4 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859089

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P859089

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	351275
5°	352617
10°	353687
15°	353695
20°	351763
25°	343520
30°	321069
35°	278041
40°	217194
45°	155828
50°	101239
55°	60594
60°	35456
65°	22762
70°	15158
75°	11440
80°	8561
85°	0



TEST NUMBER: P859089

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	272.3	6.1
10°-20°	784.6	17.7
20°-30°	1157.8	26.1
30°-40°	1142.5	25.8
40°-50°	699.2	15.8
50°-60°	268.1	6.0
60°-70°	83.8	1.9
70°-80°	24.6	0.6
80°-90°	3.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2214.6	49.9
0°-40°	3357.1	75.7
0°-60°	4324.4	97.5
0°-90°	4436.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4436.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2859	
5°	2859	272
15°	2781	785
25°	2534	1158
35°	1854	1143
45°	897	699
55°	283	268
65°	78	84
75°	24	25
85°	0	3
90°	0	



TEST NUMBER: P859089

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2859.3
2.5°	2865.3
5°	2859.3
7.5°	2853.2
10°	2835.2
12.5°	2811.1
15°	2780.9
17.5°	2744.8
20°	2690.6
22.5°	2630.6
25°	2534.2
27.5°	2413.7
30°	2263.3
32.5°	2076.8
35°	1853.9
37.5°	1607.1
40°	1354.3
42.5°	1119.6
45°	896.9
47.5°	698.1
50°	529.7
52.5°	391.4
55°	282.9
57.5°	198.6
60°	144.3
62.5°	108.5
65°	78.3
67.5°	60.3
70°	42.2
72.5°	30.1
75°	24.1
77.5°	12.1
80°	12.1
82.5°	6.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)