

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859090

Luminaire Tested: **LX4C55D010 EX4C559030 4LBMLI**

Issue Date: 1/26/2022



Test Information

Test Method: LM-79-08
Report Number: P859090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER
Issue Date: 1/26/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C55D010 EX4C559030 4LBMLI
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 4LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5534.9 lumens
Efficiency: N/A
Efficacy: 86.6 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859090

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P859090

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	110	108		112	110	108	106		106	104	103		102	101	100		99	98	97
2	109	105	102	99		107	103	100	98		100	98	95		97	95	93		95	93	92
3	105	99	95	92		103	98	94	91		95	92	89		93	90	88		91	89	87
4	101	94	89	86		99	93	88	85		91	87	84		89	86	83		87	84	82
5	96	89	84	80		95	88	84	80		87	82	79		85	81	79		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	78	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	68		84	77	72	68		76	71	68		75	71	68		74	70	67
9	82	74	69	65		81	73	68	65		72	68	65		72	68	65		71	67	64
10	79	71	66	62		78	70	65	62		69	65	62		69	65	62		68	64	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1749913
5°	1574745
10°	1220766
15°	883583
20°	611814
25°	446026
30°	324077
35°	191775
40°	80652
45°	25140
50°	3268
55°	1821
60°	2089
65°	2471
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P859090

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1122.5	20.3
10°-20°	1921.7	34.7
20°-30°	1527.3	27.6
30°-40°	808.5	14.6
40°-50°	139.3	2.5
50°-60°	10.4	0.2
60°-70°	5.2	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4571.5	82.6
0°-40°	5380.1	97.2
0°-60°	5529.7	99.9
0°-90°	5534.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5534.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	14244	
5°	12769	###
15°	6947	1922
25°	3290	1527
35°	1279	809
45°	145	139
55°	8	10
65°	8	5
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P859090

CATALOG NUMBER: LX4C55D010 EX4C559030 4LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	14243.9
2.5°	13877.2
5°	12769.3
7.5°	11320.2
10°	9785.8
12.5°	8302.6
15°	6947.1
17.5°	5685.5
20°	4679.7
22.5°	3912.5
25°	3290.4
27.5°	2787.5
30°	2284.5
32.5°	1773.1
35°	1278.7
37.5°	844.0
40°	502.9
42.5°	289.9
45°	144.7
47.5°	51.2
50°	17.1
52.5°	17.1
55°	8.5
57.5°	8.5
60°	8.5
62.5°	8.5
65°	8.5
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)