

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858652

Luminaire Tested: **LD4C30W2N2765D010 4LBMH_4000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858652
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2765D010 4LBMH_4000K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2458.0 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858652

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P858652

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	299431
5°	295074
10°	282743
15°	267055
20°	249278
25°	226294
30°	188928
35°	136868
40°	85672
45°	48978
50°	25534
55°	14308
60°	9116
65°	5407
70°	3987
75°	1756
80°	2618
85°	0



TEST NUMBER: P858652

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	224.3	9.1
10°-20°	588.4	23.9
20°-30°	756.1	30.8
30°-40°	568.9	23.1
40°-50°	228.5	9.3
50°-60°	64.9	2.6
60°-70°	20.6	0.8
70°-80°	5.8	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1568.7	63.8
0°-40°	2137.6	87.0
0°-60°	2431.1	98.9
0°-90°	2458.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2458.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2437	
5°	2393	224
15°	2100	588
25°	1669	756
35°	913	569
45°	282	228
55°	67	65
65°	19	21
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P858652

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2437.3
2.5°	2422.4
5°	2392.7
7.5°	2337.1
10°	2266.5
12.5°	2181.4
15°	2099.7
17.5°	2006.9
20°	1906.7
22.5°	1799.3
25°	1669.4
27.5°	1513.5
30°	1331.8
32.5°	1127.7
35°	912.6
37.5°	712.2
40°	534.2
42.5°	393.2
45°	281.9
47.5°	193.0
50°	133.6
52.5°	92.8
55°	66.8
57.5°	48.2
60°	37.1
62.5°	26.0
65°	18.6
67.5°	14.8
70°	11.1
72.5°	7.4
75°	3.7
77.5°	3.7
80°	3.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)