

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858653

Luminaire Tested: **LD4C30W2N2765D010 4LBMH_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858653
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2765D010 4LBMH_5000K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2552.1 lumens
Efficiency: N/A
Efficacy: 64.4 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858653

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858653

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	310881
5°	306358
10°	293559
15°	277268
20°	258809
25°	234942
30°	196163
35°	142103
40°	88959
45°	50854
50°	26509
55°	14865
60°	9460
65°	5610
70°	4167
75°	1851
80°	2759
85°	0



TEST NUMBER: P858653

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.8	9.1
10°-20°	610.9	23.9
20°-30°	785.0	30.8
30°-40°	590.7	23.1
40°-50°	237.2	9.3
50°-60°	67.4	2.6
60°-70°	21.4	0.8
70°-80°	6.1	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1628.7	63.8
0°-40°	2219.4	87.0
0°-60°	2524.1	98.9
0°-90°	2552.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2552.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2530	
5°	2484	233
15°	2180	611
25°	1733	785
35°	948	591
45°	293	237
55°	69	67
65°	19	21
75°	4	6
85°	0	1
90°	0	



TEST NUMBER: P858653

CATALOG NUMBER: LD4C30W2N2765D010 4LBMH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2530.5
2.5°	2515.1
5°	2484.2
7.5°	2426.4
10°	2353.2
12.5°	2264.8
15°	2180.0
17.5°	2083.7
20°	1979.6
22.5°	1868.1
25°	1733.2
27.5°	1571.4
30°	1382.8
32.5°	1170.8
35°	947.5
37.5°	739.5
40°	554.7
42.5°	408.3
45°	292.7
47.5°	200.4
50°	138.7
52.5°	96.3
55°	69.4
57.5°	50.1
60°	38.5
62.5°	27.0
65°	19.3
67.5°	15.4
70°	11.6
72.5°	7.7
75°	3.9
77.5°	3.9
80°	3.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)