

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858662

Luminaire Tested: **LD4C30W2N2765D010 4LBNH_3000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858662
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2765D010 4LBNH_3000K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, W2N2765 LEDS
AND 4LBNH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2144.0 lumens
Efficiency: N/A
Efficacy: 54.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858662

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P858662

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	113	111	108	106		111	109	106	104		104	103	101			101	99	98			97
2	108	103	99	96		106	101	98	94		98	95	92			95	93	90			92
3	102	96	91	87		100	95	90	86		92	88	85			90	86	84			87
4	97	90	84	80		95	89	83	79		86	82	78			84	81	78			83
5	92	84	78	74		91	83	78	73		81	76	73			80	75	72			78
6	88	79	73	69		86	78	72	68		77	72	68			75	71	67			74
7	83	74	68	64		82	73	68	64		72	67	63			71	66	63			70
8	79	70	64	60		78	69	64	60		68	63	59			67	63	59			66
9	76	66	60	56		75	66	60	56		65	59	56			64	59	56			63
10	72	62	57	53		71	62	57	53		61	56	53			60	56	52			60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	337650
5°	329296
10°	303838
15°	269001
20°	233576
25°	199779
30°	164712
35°	108463
40°	58312
45°	25818
50°	10474
55°	7539
60°	4791
65°	3430
70°	2838
75°	1851
80°	2759
85°	0



TEST NUMBER: P858662

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.2	11.5
10°-20°	589.4	27.5
20°-30°	675.2	31.5
30°-40°	453.6	21.2
40°-50°	129.6	6.0
50°-60°	31.7	1.5
60°-70°	12.1	0.6
70°-80°	4.6	0.2
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1511.7	70.5
0°-40°	1965.4	91.7
0°-60°	2126.7	99.2
0°-90°	2144.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2144.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2748	
5°	2670	247
15°	2115	589
25°	1474	675
35°	723	454
45°	149	130
55°	35	32
65°	12	12
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P858662

CATALOG NUMBER: LD4C30W2N2765D010 4LBNH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2748.4
2.5°	2728.9
5°	2670.2
7.5°	2564.6
10°	2435.6
12.5°	2271.3
15°	2115.0
17.5°	1950.9
20°	1786.6
22.5°	1630.3
25°	1473.8
27.5°	1329.2
30°	1161.1
32.5°	938.2
35°	723.2
37.5°	527.7
40°	363.6
42.5°	238.5
45°	148.6
47.5°	89.9
50°	54.8
52.5°	43.0
55°	35.2
57.5°	27.4
60°	19.5
62.5°	15.6
65°	11.8
67.5°	7.9
70°	7.9
72.5°	3.9
75°	3.9
77.5°	3.9
80°	3.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)