

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858671

Luminaire Tested: **LD4C30W2N2765D010 4LBNLI_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858671
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2765D010 4LBNLI_5000K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2765 LEDS
AND 4LBNLI TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2498.0 lumens
Efficiency: N/A
Efficacy: 63.1 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858671

CATALOG NUMBER: LD4C30W2N2765D010 4LBNLI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858671

CATALOG NUMBER: LD4C30W2N2765D010 4LBNLI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10			50	30	10			50
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111			106	106	106			102
1	114	112	110	108		112	110	108	106		106	104	103			102	101	100			99
2	109	105	102	99		107	103	100	98		100	98	95			97	95	93			95
3	105	99	95	92		103	98	94	91		95	92	89			93	90	88			91
4	101	94	89	86		99	93	88	85		91	87	84			89	86	83			87
5	96	89	84	80		95	88	84	80		87	82	79			85	81	79			83
6	92	85	80	76		91	84	79	76		83	78	75			81	78	75			80
7	89	81	76	72		88	80	75	72		79	75	71			78	74	71			77
8	85	77	72	68		84	77	72	68		76	71	68			75	71	68			74
9	82	74	69	65		81	73	68	65		72	68	65			72	68	65			71
10	79	71	66	62		78	70	65	62		69	65	62			69	65	62			68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	789751
5°	710697
10°	550940
15°	398770
20°	276119
25°	201297
30°	146257
35°	86551
40°	36405
45°	11345
50°	1472
55°	835
60°	958
65°	1134
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P858671

CATALOG NUMBER: LD4C30W2N2765D010 4LBNLI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	506.6	20.3
10°-20°	867.3	34.7
20°-30°	689.3	27.6
30°-40°	364.9	14.6
40°-50°	62.8	2.5
50°-60°	4.7	0.2
60°-70°	2.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2063.2	82.6
0°-40°	2428.1	97.2
0°-60°	2495.6	99.9
0°-90°	2498.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2498.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6428	
5°	5763	507
15°	3135	867
25°	1485	689
35°	577	365
45°	65	63
55°	4	5
65°	4	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P858671

CATALOG NUMBER: LD4C30W2N2765D010 4LBNLI_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	6428.4
2.5°	6262.9
5°	5762.9
7.5°	5108.9
10°	4416.4
12.5°	3747.1
15°	3135.3
17.5°	2565.9
20°	2112.0
22.5°	1765.7
25°	1485.0
27.5°	1258.0
30°	1031.0
32.5°	800.2
35°	577.1
37.5°	380.9
40°	227.0
42.5°	130.8
45°	65.3
47.5°	23.1
50°	7.7
52.5°	7.7
55°	3.9
57.5°	3.9
60°	3.9
62.5°	3.9
65°	3.9
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)