

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858679

Luminaire Tested: **LD4C30W2N2765D010 4LBWH_2700K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858679
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C30W2N2765D010 4LBWH_2700K
Description: 4 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, W2N2765 LEDS
AND 4LBWH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2459.0 lumens
Efficiency: N/A
Efficacy: 62.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 39.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858679

CATALOG NUMBER: LD4C30W2N2765D010 4LBWH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P858679

CATALOG NUMBER: LD4C30W2N2765D010 4LBWH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	97	96		96
2	105	100	95	91	103	98	93	90	95	91	88		91	88	86		89
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	64	74	68	64		72	67	63		70
6	81	71	64	58	80	70	63	58	68	62	58		67	61	57		65
7	76	65	58	53	75	65	58	53	63	57	53		62	56	52		61
8	72	60	53	49	70	60	53	49	59	53	48		58	52	48		57
9	68	56	49	45	66	56	49	45	55	49	44		54	48	44		53
10	64	52	46	41	63	52	46	41	51	45	41		50	45	41		49

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	194723
5°	195467
10°	196055
15°	196072
20°	194996
25°	190426
30°	177976
35°	154131
40°	120393
45°	86384
50°	56115
55°	33585
60°	19657
65°	12616
70°	8405
75°	6361
80°	4740
85°	0



TEST NUMBER: P858679

CATALOG NUMBER: LD4C30W2N2765D010 4LBWH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.9	6.1
10°-20°	434.9	17.7
20°-30°	641.8	26.1
30°-40°	633.3	25.8
40°-50°	387.6	15.8
50°-60°	148.6	6.0
60°-70°	46.5	1.9
70°-80°	13.6	0.6
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1227.6	49.9
0°-40°	1861.0	75.7
0°-60°	2397.1	97.5
0°-90°	2459.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2459.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1585	
5°	1585	151
15°	1542	435
25°	1405	642
35°	1028	633
45°	497	388
55°	157	149
65°	43	46
75°	13	14
85°	0	2
90°	0	



TEST NUMBER: P858679

CATALOG NUMBER: LD4C30W2N2765D010 4LBWH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1585.0
2.5°	1588.3
5°	1585.0
7.5°	1581.6
10°	1571.6
12.5°	1558.3
15°	1541.6
17.5°	1521.5
20°	1491.5
22.5°	1458.2
25°	1404.8
27.5°	1338.0
30°	1254.6
32.5°	1151.2
35°	1027.7
37.5°	890.9
40°	750.7
42.5°	620.6
45°	497.2
47.5°	387.0
50°	293.6
52.5°	216.9
55°	156.8
57.5°	110.1
60°	80.0
62.5°	60.1
65°	43.4
67.5°	33.4
70°	23.4
72.5°	16.7
75°	13.4
77.5°	6.7
80°	6.7
82.5°	3.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)