

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858696

Luminaire Tested: **LD4C35W2N2050D010 4LBMH_5000K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858696
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2050D010 4LBMH_5000K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, W2N2050 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2826.0 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858696

CATALOG NUMBER: LD4C35W2N2050D010 4LBMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P858696

CATALOG NUMBER: LD4C35W2N2050D010 4LBMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	344260
5°	339261
10°	325083
15°	307043
20°	286604
25°	260168
30°	217214
35°	157370
40°	98502
45°	56309
50°	29357
55°	16450
60°	10492
65°	6192
70°	4598
75°	2041
80°	3042
85°	0



TEST NUMBER: P858696

CATALOG NUMBER: LD4C35W2N2050D010 4LBMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.8	9.1
10°-20°	676.4	23.9
20°-30°	869.3	30.8
30°-40°	654.1	23.1
40°-50°	262.7	9.3
50°-60°	74.7	2.6
60°-70°	23.7	0.8
70°-80°	6.8	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1803.6	63.8
0°-40°	2457.7	87.0
0°-60°	2795.0	98.9
0°-90°	2826.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2826.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2802	
5°	2751	258
15°	2414	676
25°	1919	869
35°	1049	654
45°	324	263
55°	77	75
65°	21	24
75°	4	7
85°	0	1
90°	0	



TEST NUMBER: P858696

CATALOG NUMBER: LD4C35W2N2050D010 4LBMH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2802.2
2.5°	2785.1
5°	2751.0
7.5°	2686.9
10°	2605.9
12.5°	2507.9
15°	2414.1
17.5°	2307.4
20°	2192.2
22.5°	2068.6
25°	1919.3
27.5°	1740.1
30°	1531.2
32.5°	1296.5
35°	1049.3
37.5°	818.8
40°	614.2
42.5°	452.1
45°	324.1
47.5°	221.9
50°	153.6
52.5°	106.7
55°	76.8
57.5°	55.5
60°	42.7
62.5°	29.9
65°	21.3
67.5°	17.1
70°	12.8
72.5°	8.5
75°	4.3
77.5°	4.3
80°	4.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)