

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P859139

Luminaire Tested: **LX4C55D010 EX4C559040 4LBWLI**

Issue Date: 2/8/2022



Test Information

Test Method: LM-79-08
Report Number: P859139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER
Issue Date: 2/8/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX4C55D010 EX4C559040 4LBWLI
Description: 4 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 4LBW TRIM WITH LI FINISH
Light Source: -
Ballast/Driver:

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5932.0 lumens
Efficiency: N/A
Efficacy: 92.8 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P859139

CATALOG NUMBER: LX4C55D010 EX4C559040 4LBWLI

Luminous Intensity Polar Plot






TEST NUMBER: P859139

CATALOG NUMBER: LX4C55D010 EX4C559040 4LBWLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	56	52	72	62	56	51	61	55	51		60	55	51		59
9	69	59	52	48	68	58	52	47	57	51	47		56	51	47		55
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P859139

CATALOG NUMBER: LX4C55D010 EX4C559040 4LBWL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	355.4	6.0
10°-20°	1121.7	18.9
20°-30°	1749.8	29.5
30°-40°	1702.6	28.7
40°-50°	850.4	14.3
50°-60°	131.7	2.2
60°-70°	15.9	0.3
70°-80°	4.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3227.0	54.4
0°-40°	4929.6	83.1
0°-60°	5911.6	99.7
0°-90°	5932.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5932.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3634	
5°	3682	355
15°	3961	1122
25°	3845	1750
35°	2765	1703
45°	1067	850
55°	109	132
65°	14	16
75°	7	4
85°	0	0
90°	0	



TEST NUMBER: P859139

CATALOG NUMBER: LX4C55D010 EX4C559040 4LBWLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	3634.5
2.5°	3648.1
5°	3682.1
7.5°	3736.5
10°	3804.6
12.5°	3892.7
15°	3960.7
17.5°	4015.1
20°	4021.9
22.5°	3974.3
25°	3845.4
27.5°	3654.9
30°	3417.1
32.5°	3118.5
35°	2765.1
37.5°	2377.7
40°	1970.1
42.5°	1535.4
45°	1066.7
47.5°	686.1
50°	414.3
52.5°	224.2
55°	108.8
57.5°	47.6
60°	27.2
62.5°	20.4
65°	13.6
67.5°	13.6
70°	6.8
72.5°	6.8
75°	6.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)