

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P858738

Luminaire Tested: **LD4C35W2N2765D010 4LBMH_6500K**

Issue Date: 11/9/2023



Test Information

Test Method: LM-79-08
Report Number: P858738
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)
Test Lab: INNOVATION CENTER-P3
Issue Date: 11/9/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD4C35W2N2765D010 4LBMH_6500K
Description: 4 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 6500K, W2N2765 LEDS
AND 4LBMH TRIM WITH FINISH

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2919.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P858738

CATALOG NUMBER: LD4C35W2N2765D010 4LBMH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P858738

CATALOG NUMBER: LD4C35W2N2765D010 4LBMH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	355587
5°	350422
10°	335774
15°	317141
20°	296030
25°	268735
30°	224364
35°	162544
40°	101741
45°	58169
50°	30332
55°	16985
60°	10836
65°	6395
70°	4741
75°	2089
80°	3113
85°	0



TEST NUMBER: P858738

CATALOG NUMBER: LD4C35W2N2765D010 4LBMH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	266.3	9.1
10°-20°	698.7	23.9
20°-30°	897.9	30.8
30°-40°	675.6	23.1
40°-50°	271.4	9.3
50°-60°	77.1	2.6
60°-70°	24.4	0.8
70°-80°	6.9	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1863.0	63.8
0°-40°	2538.6	87.0
0°-60°	2887.0	98.9
0°-90°	2919.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2919.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2894	
5°	2842	266
15°	2494	699
25°	1982	898
35°	1084	676
45°	335	271
55°	79	77
65°	22	24
75°	4	7
85°	0	1
90°	0	



TEST NUMBER: P858738

CATALOG NUMBER: LD4C35W2N2765D010 4LBMH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2894.4
2.5°	2876.7
5°	2841.5
7.5°	2775.4
10°	2691.6
12.5°	2590.5
15°	2493.5
17.5°	2383.3
20°	2264.3
22.5°	2136.7
25°	1982.5
27.5°	1797.4
30°	1581.6
32.5°	1339.2
35°	1083.8
37.5°	845.8
40°	634.4
42.5°	467.0
45°	334.8
47.5°	229.2
50°	158.7
52.5°	110.2
55°	79.3
57.5°	57.3
60°	44.1
62.5°	30.9
65°	22.0
67.5°	17.6
70°	13.2
72.5°	8.8
75°	4.4
77.5°	4.4
80°	4.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)